

SHIM-MASK®

by DeVilbiss

IDEAL FOR:

- PAINT AND CLEAR COAT RUNS
- IMPERFECTIONS
- MINIMIZING EXPOSED AREA WHEN SANDING PAINT-FILLED CHIPS OR SCRATCHES

ADVANTAGES:

- 304 STAINLESS STEEL PROVIDES DURABILITY FOR RE-USE
- CHEMICALLY ETCHED SHAPES PROVIDE SMOOTH EDGES
- CHOICE OF FOUR STENCIL SHAPES

**STAINLESS STEEL MASKING STENCIL TO PREVENT RUB-THROUGH
WHEN SANDING OR SHAVING MINOR SURFACE IMPERFECTIONS**




4 types of templates

Template types can be selected based on the size and shape of dust and debris on the paint surface.

Specifications

Product Number	SHIM-3
Thickness	50μm (0.05mm)
Size	120×120mm
Material	Stainless steel(SUS304)
Quantity	3 pieces/set



After confirming that the paint surface to which the dust and debris are attached is completely dry, perform the work procedure described below.

<p>1</p> <p>Repair defects such as paint drips.</p>	<p>5</p> <p>Scrape protruding portions using a diamond cutter.</p>	<p>9</p> <p>Apply compound to the ground area.</p>
<p>2</p> <p>Select a template that matches the shape of the paint defect.</p>	<p>6</p> <p>Perform a rough-grind work using an electric sander (#800 to 1200).</p>	<p>10</p> <p>Polish using a finishing sanding polisher.</p>
<p>3</p> <p>Scrape away high spots using a single-edge cutter. <i>Note: Take precautions while working by wearing work gloves.</i></p>	<p>7</p> <p>Switch to a larger template and grind the section using a finer sander (#2000).</p>	<p>11</p> <p>Wipe off the remaining dust with a cloth.</p>
<p>4</p> <p>Securely fix the shim mask with tape.</p>	<p>8</p> <p>Remove the mask and wipe the dust off using a cloth.</p>	<p>12</p> <p>Finished.</p>

DEVILBISS®

CFT Ransburg Japan KK

15-5, Fukuura 1-chome, Kanazawa-ku, Yokohama, Kanagawa Japan 236-0004

TEL : +81-45-785-6434 / FAX : +81-45-785-6517

Website <http://www.carlisleleft.co.jp/>

©DEVILBISS is a registered trademark of Carlisle Fluid Technologies.

©LUNA is a registered trademark of CFT Ransburg Japan KK.

For more information, please contact: